

VARTA Indestructible F20 Pro with 2AA Batt.



Extremely robust (9m drop test, IP67) LED Flashlight with two light levels impact resistance IK08 and shock absorbing rubber head and tail cap.



Information

- Extremely robust (9m drop test) flashlight with a shock-absorbing rubberized head and end cap
- Anodized type II aluminium body
- Impact resistant lens and reflector
- impact resistance rating IK08 (IEC 62262)
- Rugged construction
- 9m drop test
- Water and dust proof (IP67)
- Bright high performance LED
- 2 light levels: high and low
- Designed for maximum durability
- Operated with 2AA batteries (incl)

Article Details

Ordernumber	18711 101 421
Customs Tariff Number	85131000
Country Of Origin	China
Beam Range	(up to) 140.00 m
Runtime	(up to) 55 h
Total light output	(up to) 350 lm
Equipped with	2 x AA Longlife Power
Product Diameter mm	42.00
Product Length / Depth mm	167.00
Product Weight g	157.00

Logistical Data

	Content (SU)	GTIN / EAN	Facing (mm)	Depth (mm)	Height (mm)	Weight (kg)
VBE (Selling unit)	1	40 08496 987238	135.00	40.00	280.00	0.24
SK2 (Inner carton 2)						
SK1 (Inner carton 1)						
VSK (Master carton)	4	40 08496 987245	295.00	145.00	155.00	1.07
PAL (Pallet)	560	40 08496 987252	800.00	1,200.00	1,235.00	171.11
Layer / Pallet	Master carton / Layer		Master carton / Pallet		Minimum pieces / shipment unit	
7	20		140		4	

All mentioned products and specifications are subject to change. In case of non-availability of any product or item, VARTA Consumer Batteries GmbH & Co. KGaA cannot be held responsible. Some of the products shown may not be available in all countries. The pictures might be different to the original products. Technical changes and errors reserved.

VARTA Consumer Batteries GmbH & Co. KGaA | Alfred-Krupp-Str. 9 | 73479 Ellwangen | Germany
 P.O. Box 1363 | 73473 Ellwangen | Germany | Phone (+49) 7961 83 0 | Fax (+49) 7961 83 440

