

Technical data sheet

Article number:
111-01168

MCT50L



Product Group	Cable ties for food industry, detectable
Product Family	MCT-Series, PA66MP
Material	Polyamide 6.6, metal detectable (PA66MD)
Colour	Yellow (YE)
Bundle Ø max.	110.0 mm
Bundle Ø min.	1.5 mm
Flammability	UL 94 HB
Halogen-free	Yes
Length (L)	380.0 mm
Min.Tensile Strength	225 N
Operating Temperature	-40 °C to +85 °C
Package Content packed in	pack
Pack Cont.	100 pcs.
Thickness (T)	1.4 mm
Variant	Inside Serrated
Weight/Unit	0.00282 kg
Width (W)	4.7 mm

HF ✓

RoHS ✓