

shock absorber DYEF-M5-Y1F

Part number: 548371

FESTO



Data sheet

Feature	Value
Size	M5
Stroke	2.8 mm
Cushioning	Pneumatic cushioning with fixed metallic stop
Assembly position	Any
Position detection	No
Max. impact speed	0.8 m/s
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Ambient temperature	0 ... 60 °C
Cushioning length	2.8 mm
Max. energy consumption per stroke	0.02 J
Product weight	2.9 g
Mounting type	with lock nut
Materials note	Free of copper and PTFE Conforms to RoHS
Material seals	NBR
Material housing	High alloy steel