



Precision Brand Steel Shim Stock

ENGLISH



PRECISION BRAND Steel Shim Stock is a full hard, cold rolled, low carbon 1008-1010
 Rockwell Hardness: < .069" thick RB90 Min.: > .070" thick RB84 Min.
 Meets AISI-1008/AISI-1010
 Shim continuously marked along its length as follows:
 Shim Thickness
 Material
 Batch/Lot number
 Web address for trace ability record of Batch/Lot number

RS Code	Manufacturers Code	Thickness	Size
		Steel Shim Metric	Width x Length
518-895	77-316-971	0.05mm	150mm x 2.5m
518-918	77-316-972	0.10mm	150mm x 2.5m
518-908	77-316-973	0.15mm	150mm x 2.5m
518-879	77-316-974	0.20mm	150mm x 2.5m
518-841	77-316-975	0.25mm	150mm x 2.5m
518-845	77-316-976	0.30mm	150mm x 2.5m
518-835	77-316-977	0.40mm	150mm x 2.5m
518-863	77-316-978	0.50mm	150mm x 2.5m
519-103	77-316-979	0.65mm	150mm x 2.5m
519-135	77-316-980	0.80mm	150mm x 2.5m
		Steel Shim Inch	Width x Length
519-034	77-316-130	0.001"	6" X 100"
Not Stocked	77-316-155	0.0015"	6" X 100"
519-131	77-316-195	0.002"	6" X 100"
519-078	77-316-245	0.003"	6" X 100"
Not Stocked	77-316-280	0.004"	6" X 100"
518-930	77-316-320	0.005"	6" X 100"
Not Stocked	77-316-345	0.006"	6" X 100"
Not Stocked	77-316-370	0.007"	6" X 100"
518-756	77-316-395	0.008"	6" X 100"
518-750	77-316-450	0.010"	6" X 100"
518-813	77-316-480	0.012"	6" X 100"
518-740	77-316-530	0.015"	6" X 100"
518-744	77-316-590	0.020"	6" X 100"
518-823	77-316-630	0.025"	6" X 100"
518-902	77-316-660	0.031"	6" X 100"
518-867	77-316-999	Steel Assortment Pack Metric: Sheets 150mm x 300mm	10 piece 0.05mm to 0.80mm
518-891	77-316-680	Steel Assortment Pack Inch: 6" x 12"	12 piece 0.001" to 0.015"

Individual sizes contained in Assortment Packs marked in red