

ROBUST SCREWDRIVING

PRO

- 1 Extended torsion zone absorbs the torque stress at the bit's tip
- 2 Heat-treated modified steel for strength and resistance to high torque



* vs Bosch 2607001528



BOSCH

PRO IMPACT T SCREWDRIVER BIT

PRO


- For driving T screws efficiently, eg when installing all types of panels, equipment, and fixtures
- Highly efficient for installers, electricians, metalworkers, and woodworkers: Robust
- Up to 50x more robust than a Bosch 2607001528 Extra Hard Bit
- 1/4" Impact rated Hex shank for use in impact driver and drill driver



PRODUCT PROPERTIES		ORDERING INFORMATION				
		Packaging type	Pack quantity	Minimum order quantity	Barcode 6 949 509...	Part number
T10, 25 mm, 2 pcs		PC1d	2	5	233 356	2 608 522 472
T15, 25 mm, 2 pcs		PC1d	2	5	233 349	2 608 522 473
T20, 25 mm, 2 pcs		PC1d	2	5	233 332	2 608 522 474
T25, 25 mm, 2 pcs		PC1d	2	5	233 325	2 608 522 475
T27, 25 mm, 2 pcs		PC1d	2	5	233 318	2 608 522 476
T30, 25 mm, 2 pcs		PC1d	2	5	233 301	2 608 522 477
T40, 25 mm, 2 pcs		PC1d	2	5	233 295	2 608 522 478
T20; T25; T30, 25 mm, 3 pcs		PC1d	3	5	233 288	2 608 522 479
T20, 25 mm, 8 pcs, with Pick and Click Index		PC1a	8	5	912 150	2 608 522 380
T25, 25 mm, 8 pcs, with Pick and Click Index		PC1a	8	5	912 167	2 608 522 381
T30, 25 mm, 8 pcs, with Pick and Click Index		PC1a	8	5	912 174	2 608 522 382
T15; T20(x2); T25(x2); T30(x2); T40, 25 mm, 8 pcs, with Pick and Click Index		PC1a	8	5	851 121	2 608 522 322
T20, 25 mm, 10 x 25 pcs, with Display		P1a	25	10	980 241	2 607 002 805
T25, 25 mm, 10 x 25 pcs, with Display		P1a	25	10	980 258	2 607 002 806
T30, 25 mm, 10 x 25 pcs, with Display		P1a	25	10	980 265	2 607 002 807
T10, 55 mm, 2 pcs		PC1d	2	5	241 979	2 608 522 528


BOSCH

PRO IMPACT T SCREWDRIVER BIT

PRO

PRODUCT PROPERTIES	ORDERING INFORMATION				
	Packaging type	Pack quantity	Minimum order quantity	Barcode 6 949 509...	Part number
T15, 55 mm, 2 pcs	PC1d	2	5	241 986	2 608 522 529
T20, 55 mm, 2 pcs	PC1d	2	5	241 993	2 608 522 530
T25, 55 mm, 2 pcs	PC1d	2	5	242 006	2 608 522 531
T30, 55 mm, 2 pcs	PC1d	2	5	242 013	2 608 522 532
T40, 55 mm, 2 pcs	PC1d	2	5	242 020	2 608 522 533
T10; T15; T20, 55 mm, 3 pcs	PC1d	3	5	242 037	2 608 521 U54
T25; T30; T40, 55 mm, 3 pcs	PC1d	3	5	242 044	2 608 521 U55
T15; T20(x2); T25(x2); T30(x2); T40, 55 mm, 8 pcs, with Pick and Click Index	PC1a	8	5	851 190	2 608 522 329
T25, 55 mm, 15 pcs, with Display	P1k	15	10	242 051	2 608 522 534
T20, 90 mm	PC1d	1	5	242 068	2 608 522 535
T25, 90 mm	PC1d	1	5	242 075	2 608 522 536
T30, 90 mm	PC1d	1	5	242 082	2 608 522 537
T20, 150 mm	PC1d	1	5	242 099	2 608 522 538
T25, 150 mm	PC1d	1	5	242 105	2 608 522 539


BOSCH