

Superior cut and chemical protection combined

- **Specialized protection:** AlphaTec® 58-835 chemical gloves' nitrile barrier protects against common chemicals
- **Enhanced features:** Their orange visible inner liner indicates when the shell is compromised, warning users.
- **Heightened defenses:** AlphaTec® 58-835 safety gloves' INTERCEPT™ Cut Resistance liner ensures EN ISO CUT F & ANSI/ISEA 105-2024 CUT A6 protection
- **Tightened grip:** ANSELL GRIP™ nitrile shell treatment delivers better grip for handling both wet and oily components
- **Optimized durability:** AlphaTec® 58-835 gloves achieve ANSI/ISEA 105-2024 ABRASION LEVEL 5 and EN ABRASION LEVEL 4 resistance, for longer wear
- **Elevated comfort and dexterity:** Higher gauge yarns and increased use of HPPE lead to a dramatic increase in comfort, tactility and dexterity
- **Harm-free food handling:** These AlphaTec® chemical and cut resistant gloves comply with EU and FDA food handling regulations



Industries

- Automotive
- Recycling and Waste Disposal
- Chemical
- Energy
- Metal fabrication

Applications

- Handling metal sheets & panels
- Handling materials with sharp or rough edges
- Removal of broken glassware
- Spill or leakage cleanup
- Assembling and mounting components
- Handling application & cleaning tools
- Transport of hazardous substances
- Handling sharp metal parts

Key Features

- **Nitrile shell barrier:** EN ISO 374 Type A resistance against common chemicals
- **Orange visible indicator inner liner:** Indicates when chemical protective gloves are cut, for superior safety
- **INTERCEPT™ Cut Resistance Technology:** EN ISO CUT F & ANSI/ISEA 105-2024 CUT A6 protection



Performance Standards

ANSI/ISEA 105-2024



CE 0493

Category III

EN388: 2016



4X43F

EN 407



X1XXXX

EN ISO 374-1:2016



AJJKLMNOPT

EN ISO 374-5:2016



UK
CA

Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec® 58-835	Liner Material: HPPE, Nylon, Engineered Yarns Coating Material: Nitrile + PI	6, 7, 8, 9, 10, 11	350 / 13.8	Grey	6 pairs per bag, 12 bags per carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.