

192A.20G | 192A.G - High-performance diagonal cutters



Description:

- New head design to increase durability and cutting capacity
- Cutting edges designed to cleanly cut all types of wire: soft wires and modern materials to a maximum piano wire specification of: 192A.16G: 2.0mm 210 kg/mm² 192A.20G: 2.5mm 200 kg/mm²
- High Mechanical advantage due to off-set rivet and cutting edge geometry reducing effort.

=0	192A.20G
Diameter D Maxi [mm]	2.5
Length L [mm]	200.0
Thickness E [mm]	2.5
Head Height C [mm]	22.0
Head Width B [mm]	28