

This smart hands-free head torch has 6 bright LEDs so it is bound to be strong. With 80 lumens of brightness and a beam range of 32 metres, it helps light up dark places for night runners, cyclists, dog walkers and professional tradesmen. For ease of operation and comfort it has a front switch and two-way adjustable strap to fit any head size. A battery pack on the back of the headband holds three AAA batteries (supplied), which have a maximum possible burn time of 20 hours. Even when batteries are fitted the E41 weighs only 120g so it is light enough to be worn for sustained periods.

- Hands-free head torch
- 6 energy-efficient LED Light Chips
- Easy-access front switch
- Round and overhead adjustable head straps
- Ideal for home, leisure and work use
- Supplied with: Batteries (3 x AAA)

Technical Information

E41	BOOST	POWER	LOW POWER
POWER	x	80 lumens	x
BEAM DISTANCE	x	32 metres	x
RUN TIME	x	20 hours	x
SIZE	x	WEIGHT	120g

Supplied with : Batteries (3 x AAA)

Code	Description	Packaging	Barcode
7041TBCC	E41 - Cut case of 6	Try-Me Pack (Blue/Yellow)	4029113704106

RRP EACH	ex.vat £16.63 / incl.vat £19.95
RRP Cut Case	ex.vat £99.78 / incl.vat £119.74



LEDLITES E41