

Product Information



5525UAI075L51-11

EAN 4031582310665

Swivel castor with wheel brake, housing made of Polyamide, with blind hole for furniture fittings.
Wheel centre made of Polyamide, Tread: Polyurethane, plain bearing

Technical Data	
Wheel diameter	75 mm
Width of Tread	10 mm
Castor width	65 mm
Centre hole	11 mm
Dome-Ø	45 mm
Swivel Interference	212 mm
Overall height	88 mm
Temperature	- 10 / + 40 °C
Standard	EN 12528
Weight	0.31 kg
Swivel Radius	106 mm
Hardness of tread	A 87 Shore
Load capacity	100 kg
Load capacity (static)	200 kg



Roll performance	+	+	+	+	+
Movement noise	+	+	+	+	+
Attrition	+	+	+	+	+
Corrosion resistance	+	+	+	+	+

Product Information



5525UAI075L51-11

EAN 4031582310665

