



Kingston Technology FURY Beast 32GB 6000MT/s DDR5 CL36 DIMM (Kit of 2) RGB EXPO

Brand : Kingston Technology

Product family: FURY

Product code:

KF560C36BBE2AK2-32

Product name : 32GB

6000MT/s DDR5 CL36 DIMM (Kit of 2) FURY Beast RGB EXPO

- Enhanced RGB lighting with new heat spreader design*
- Patented Kingston FURY Infrared Sync Technology™
- Intel® XMP 3.0 Certified
- AMD EXPO™ Certified
- Qualified by the world's leading motherboard manufacturers**
- Improved stability for overclocking

32GB 6000MT/s DDR5 CL36 DIMM (Kit of 2) FURY Beast RGB EXPO

Kingston Technology FURY Beast 32GB 6000MT/s DDR5 CL36 DIMM (Kit of 2) RGB EXPO. Component for:

PC/Server, Internal memory: 32 GB, Memory layout (modules x size): 2 x 16 GB, Internal memory type:

DDR5, Memory clock speed: 3000 MHz, Memory form factor: 288-pin DIMM, CAS latency: 36



Features		Features	
Buffered memory type	Unregistered (unbuffered)	Backlight colour	Red/Green/Blue
On-Die ECC	✓	Operational conditions	
CAS latency	36	Operating temperature (T-T)	0 - 85 °C
Internal memory *	32 GB	Storage temperature (T-T)	-55 - 100 °C
Memory layout (modules x size) *	2 x 16 GB	Weight & dimensions	
Internal memory type *	DDR5	Width	7.1 mm
Memory clock speed *	3000 MHz	Depth	133.4 mm
Memory data transfer rate	6000 MT/s	Height	42.2 mm
Component for *	PC/Server	Weight	90 g
Memory form factor *	288-pin DIMM	Packaging data	
ECC *	✗	Package width	121.9 mm
Memory ranking	1	Package depth	14 mm
Memory voltage	1.35 V	Package height	171.5 mm
AMD Extended Profiles for Overclocking (EXPO)	✓	Package weight	133.1 g
SPD profile	✓	Logistics data	
Country of origin	China, Taiwan	Master (outer) case width	190.5 mm
Cooling type	Heatsink	Master (outer) case length	254 mm
Lead plating	Gold	Master (outer) case height	177.8 mm
Backlight	✓	Master (outer) case gross weight	1.51 kg
		Products per master (outer) case	10 pc(s)



0740617345902



740617345902

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 22-OCT-2024. Prints or copies of Information are only valid on the printed Publication date