

RP2RCF

Mono 1/4" right-angle plug with pan head



Article Variations

Article Name	Details	Packaging
RP2RCF	Nickel Housing,Nickel plated contacts	Plastic Packaging
RP2RCF-D	Nickel Housing,Nickel plated contacts	BULK
RP2RCF-B	Black Housing,Gold plated contacts	Plastic Packaging
RP2RCF-B-D	Black Housing,Gold plated contacts	BULK
RP2RCF-BAG	Black Housing,Nickel plated contacts	Plastic Packaging
RP2RCF-BAG-D	Black Housing,Nickel plated contacts	BULK

Technical information

Product

Title	RP2RCF
Connection Type	Plug

Electrical

Contact resistance	depends on mating connector mΩ
Dielectric strength	0.5 kV dc
Insulation resistance	> 1 GΩ

Mechanical

Lifetime	> 1000 mating cycles
Insertion and Withdrawal force	≤ 60N
Cable O.D.	4 - 7 mm

Material

Sleeve & Inner	Brass
Sleeve plating	Nickel
Inner plating	Nickel / Gold
Shell	Steel
Shell plating	Nickel / Black

Environmental

Temperature range	-20 °C to +70 °C
Flammability	UL 94 HB
Solderability	complies with IEC68-2-20