

**22.311-XM-@****(TEST LEAD, STRAIGHT 4MM BANANA PLUGS, SHROUDED, 32A)**

- The 22.311 test lead is a **CE** Certified Test Lead with straight shrouded 4mm banana plug on each end.
- Uses 14 AWG PVC wire.
- Length is designated in meters by the “X” in the part number.  
Available lengths are: 0.25m and 1m
- Ratings:
  - Operating Voltage: 1000V (CATIII)
  - Current: 32 Amps
  - Contact Resistance:  $\leq 0.0005\Omega$
  - Insulation Resistance:  $\geq 500M\Omega$
- Materials:
  - Banana Body: Nickel Plated Brass
  - Cage Spring: Nickel Plated Beryllium Copper
- Color: The “@” in the model number represents color. Available colors:  
-0 Black, -2 Red
- RoHS 3 Compliant, **CE** Certified