

FEATURES

- Low voltage power lamp for cost saving energy efficiency
- Anti-glare louvre for added comfort
- Die cast head for extra protection
- Re-enforced tempered glass lens

RS PRO Halogen Machine Light, 240 V, 55 W, Articulated, 830mm Reach, 830mm Arm Length

RS Stock No.: 433-3045



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From our high quality RS Pro brand, this halogen task light is a perfect addition to your workstation. With an energy efficient halogen bulb, the machine light has a bright output, so you can enjoy shadow-free lighting for clear and comfortable working. The machine light features an adjustable arm, with three points of articulation to ensure you have the light you need where you need it. There is even a built in handle on the light head for further ease of adjustment, with an on/off switch located on the head for extra convenience

General Specifications

Lamp Type	Halogen
Light Style	Articulated Arm
Lamp Supplied	Yes
Integral transformer	Yes
Shield Fitted	No
Switch Fitted	Yes on head
service life	up to 40,000hours
Arm Type	Adjustable

Electrical Specifications

Voltage Rating	240VAC
Wattage	55W
EU Energy Efficiency Rating	C
Number of Bulbs	1

Mechanical Specifications

Arm Length	830mm
Cable Length	1.8m
Maximum Reach	830mm

Protection Category

IP Rating

IP 65

Approvals

Compliance/Certifications

RoHS Certificate of Compliance

