

## FEATURES

- Low voltage power lamp for cost saving energy efficiency
- LEDs are long lasting and produce no heat
- Re-enforced tempered glass lens provides impact resistance
- Robust build for a long service

## RS PRO LED Machine Light, 100 → 260 V ac, 12 W, Adjustable Arm

RS Stock No.: 777-7978



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

From our high quality RS Pro brand, this LED task light is perfect addition to your workstation. With six efficient LED bulbs, the machine light has a bright, white output, so you can enjoy shadow-free lighting for clear and comfortable working.

The LED light features an adjustable arm, with a single point of articulation to ensure you have the light you need where you need it. There is even a built in handle on the light head for further ease of adjustment.

### General Specifications

Lamp Type	LED
Light Style	Articulated Arm
Lamp Supplied	Yes
Integral transformer	Yes
Shield Fitted	No
Switch Fitted	No
service life	up to 40,000hours
Arm Type	Adjustable

### Electrical Specifications

Mains Plug Type	Type C – Euro plug
Voltage Rating	100VAC to 260VAC
Wattage	12W
EU Energy Efficiency Rating	C
Number of Bulbs	6
Colour Temperature	5700K

### Mechanical Specifications

Cable Length	1.8m
Beam Angle	60°

## Operation Environment Specifications

Temperature Range	-30°C to 60°C
-------------------	---------------

## Protection Category

IP Rating	IP 65
-----------	-------

## Approvals

Compliance/Certifications	RoHS Certificate of Compliance , CE Approved
---------------------------	--



