


**960KPC**

## Reversible impulse extractor with adjustable torque for glow plugs



420x185x60 mm - 2,8 kg

### Features:

- Pneumatic extractor with adjustable torque and special sockets allow jammed glow plugs to be unscrewed, thereby minimizing damage risk
- 5 1/4" impact sockets, long series, specially designed for glow plugs: 8-9-10-11-12 mm, 2 extensions and 1 articulated joint
- 4 adjustable driving torques: 10-20-30-40 Nm
- Right-hand and left-hand adjustment

Prevents glow plugs from being broken during disassembly.



|  | art.   |                                                                                                   |     |
|---------------------------------------------------------------------------------|--------|---------------------------------------------------------------------------------------------------|-----|
| 009600780                                                                       | 960KPC |  8-9-10-11-12 mm | 2,8 |

