



LED lamp Yellow 115 V

Model		
product brand name	SETRON	
product designation	LED lamp	
type of light source	LED	
socket design	others	
type of voltage of the operating voltage for actuation	AC/DC	
Supply voltage		
operating voltage		
• at AC at 50 Hz rated value minimum	115 V	
• at AC at 50 Hz rated value maximum	115 V	
• at AC at 60 Hz rated value minimum	115 V	
• at AC at 60 Hz rated value maximum	115 V	
• at DC rated value minimum	115 V	
• at DC rated value maximum	115 V	
Appearance		
color of the light source	yellow	
Product details		
product component		
• diode	Yes	
• lamp transformer	No	
• light source	Yes	
• series resistor	No	
Connections		
type of electrical connection for auxiliary circuit	others	
Mechanical Design		
fastening method	others	
net weight	4 g	
Approvals Certificates		
General Product Approval	other	Environment



[Confirmation](#)

[Environmental Con-
firmations](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5TG8057-2>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5TG8057-2>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5TG8057-2

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

12/19/2020 

