



**Part Number :** [1301370089](#)

**Product Description :** Super-Safeway Multiple Outlet Box, Standard Depth, 2-Sided, NEMA 5-20 Duplex Receptacles, Cord Clamp, Duplex Cover Plates

**Series Number :** 130137

**Status :** Active

**Product Category :** Power Distribution

**Engineering Number :** 3000-10



---

## Documents & Resources

---

### Product Environment Compliance

#### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Reviewed per EU 2015/863

#### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

## Part Details

### General

Status	Active
Category	Power Distribution
Series	130137
Description	Super-Safeway Multiple Outlet Box, Standard Depth, 2-Sided, NEMA 5-20 Duplex Receptacles, Cord Clamp, Duplex Cover Plates
Enclosure Rating	N/A
NEMA Configuration	NEMA 5-20
Product Name	Super-Safeway
Type	Multiple Outlet Box
UPC	78678833643

### Agency

CSA	LR6837
UL	E46237

### Electrical

Current - Maximum per Contact	20.0A
GFCI	No
GFCI Reset	N/A
Ground Continuity Monitor	No
Open Neutral Relay	N/A
Voltage - Maximum	125V

### Physical

Cord Diameter	8.26-16.64mm (.325-.655")
Cord Grip Body Size	Double C-Clamp
Cord Length	N/A
Cord Type	N/A
Feed-Thru	No
Flip Lid	No

Material - Housing	Rubber
Mounting Style	Portable
Net Weight	602.370/g
Number of Receptacles	2
Packaging Type	Carton
Receptacle Type	Duplex