


PXV0732/P Datasheet

Product Name // Vitalis Buccaneer Inline Range (3 Contact)

 [View Product Page](#)



// Product Description:

- ✧ PXV0732/P provides a PCF reduction of 4.5 kg CO₂e per 100 units compared to the equivalent Standard Series Buccaneer part number
- ✧ Inline Cable Connector
- ✧ Water and dustproof to IP68 when mated with compatible connectors
- ✧ Plug contacts
- ✧ 3 pole with leading Earth contact
- ✧ Screw contacts, supplied fitted
- ✧ 6mm-8mm diameter cable acceptance
- ✧ Cable Glands for differing cable diameters available separately individually or in packs
- ✧ Cable Support accessory 12237/R available separately
- ✧ PXV0733 Sealing Cap available separately to maintain IP rating of unmated connectors
- ✧ Mates with Standard Vitalis Series (PXV) and Standard Series (PX) Buccaneer Flex Connectors

// General Information:

Product Display Title:	Vitalis Buccaneer Inline Range (3 Contact)
Product Family:	Circular Power Connector
Product Series:	Standard Vitalis Buccaneer
Approvals:	UL, VDE
Body Colour:	Black
Body Material:	Polyamide (PA)- Glass Filled
Body Material Type:	Plastic Body
Contact Type:	Plug Contact
Coupling Type:	Screw
Current Max:	10A, 12A
Diameter Over Coupling Ring Mm:	38.1mm
Flamability Rating:	UL94HB
Function:	Inline Cable Connector
Insert Colour:	Black Insert And Gland Nut
Ip Rating:	IP68, IP69K
Max Cable Entry Size:	8mm
Min Cable Entry Size:	6mm
Max Contact Accomodation Awg:	12AWG
Min Contact Accomodation Awg:	14AWG
Max Contact Accomodation Mm2:	4mm2
Min Contact Accomodation Mm2:	2.5mm2
Max Operating Temperature:	+70°C
Min Operating Temperature:	-20°C
Number Of Contacts:	3 Contacts
Rohs Compliant:	Yes
Voltage Max:	277V

// Product PDF Links

 [Standard Vitalis Buccaneer Product...](#)

// Product 3D CAD Model Links

 [PXV0732/P3D CAD Model](#)



Have a question or project enquiry
you'd like to talk to us about?



[Click Here To Contact Us](#)