

1670720-5 ✓ ACTIVE

AMP | HDSCS

TE Internal #: 1670720-5

TE Internal Description: SLIDE, TAB HSG GROUP C

HDSCS FIXING SLIDES

[View on TE.com >](#)



Connectors > Automotive, Truck, Bus, & Off-Road Connectors > Connector Accessories > Other Connector Accessories > HDSCS FIXING SLIDES



Accessory Type: **Mounting Clip**

Connector System: **Wire-to-Wire**

Material: **PBT GF**

Color: **Gray**

Number of Positions: **2, 6, 7, 8**

[All HDSCS FIXING SLIDES \(21\)](#)

Features

Product Type Features

Accessory Type	Mounting Clip
Connector System	Wire-to-Wire

Configuration Features

Number of Positions	2, 6, 7, 8
---------------------	------------

Body Features

Material	PBT GF
Color	Gray

Usage Conditions

Operating Temperature Range	-40 – 140 °C[-40 – 284 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2019 (201) Candidate List Declared Against: JUL 2019 (201) Does not contain REACH SVHC
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2019 (201) Candidate List Declared Against: JUL 2019 (201)
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



Also in the Series | **HDSCS**



Automotive Connector Caps & Covers(19)



Automotive Seals & Cavity Plugs(1)



Automotive, Truck, Bus, & Off-Road Housings(189)



Other Automotive Connector Accessories(22)


Customers Also Bought



TE Model / Part #9-2141157-1
SHIELD CRIMP FERRULE, 90DEG



TE Model / Part #2141809-3
CONTACT KIT, BODY AND SPRING,



TE Model / Part #926330-8
6P POS-LOCK BU GEH



TE Model / Part #1-2322122-2
HVP800 2P HEADER ASSY



TE Model / Part #2-2322122-1
HVP800 2P HEADER ASSY



TE Model / Part #2177090-1
STEEL, OUTER FERRULE, 8MM HV, 50SQMM



TE Model / Part #2315855-4
MSD, REC HSG ASSY, 450A, V0, M8



TE Model / Part #2315855-6
MSD, REC HSG ASSY, 630A, V0, M8



TE Model / Part #2315856-4
MSD, PLUG HSG ASSY, 450A, V0



TE Model / Part #5-2322122-1
HVP800 2P HEADER ASSY

Documents

Product Drawings

SLIDE, TAB HSG GROUP C

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1670720-5_K.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1670720-5_K.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1670720-5_K.3d_stp.zip](#)

English

Datasheets & Catalog Pages

[HDSCS Catalog](#)

English

Product Specifications

[Application Specification](#)

English