

COMBINATION SPANNER AF 1"



- A ring and open ended spanner combined with the same size opening at each end
- Off set at 15° for easier use on flat surfaces
- TengTools hip grip design for contact with the flat side of the fastening
- Chrome vanadium satin finish
- Designed and manufactured to ASME B107.100

Combination Spanner 1"

General information

Country of origin: Taiwan
Barcode: 5020385040618
Tariff code Europe: 8204110000
ECCN US: EAR99
ETIM: EC002176
UNSPSC: 27111713

Dimensions

Net weight (g): 302
Length: 290 mm

Attributes

Product type: Combination Spanners
Material: CrV
Certificates: N/A
Size: 1"
Tethering facility: No
Spanner type: Regular
Unit of measurement: AF
Jaw diameter: 52.0
Jaw height (mm): 8.9
Offset angle jaw (°): 15
Ring diameter (mm): 36.9
Ring height (mm): 12.5
Offset angle ring (°): 15

Features



DESIGNED IN SWEDEN

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.



Sandbergsvägen 3
441 39 Alingsås, Sweden