



Product data sheet

Power tools for trade & industry

Planer

PRO GHO 20-82



Experience control and comfort for a smooth finish

The most important data

Rated input power	700 W
Planing width	82 mm
Planing depth	0 – 2 mm

Part Number 0 601 5A9 170

Technical data

Technical data

Rated input power	700 W
Planing depth	0 – 2 mm
Weight	2.7 kg
Adjustable rebating depth	0 – 9 mm
No-load speed	16,500 rpm
Planing width	82 mm
Packaging dimensions (width x length x height)	160 x 262 x 174 mm
Voltage, electrical	230 V

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Smooth and flat finish enabled by consistent depth control mechanism and precisely machined flat aluminium base Controlled planing due to compact design and optimised centre of gravity for steady planing Eliminates wood chip blockage via improved airflow design and providing flexibility to discard wood chips from either right or left side

**HEAVY
DUTY****700
W**

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

