

MOTION CONNECT 300

MLFB-Ordering data

6FX3002-5CL12-1AF0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Electrical data	
No. of cores x cross-section mm²	4 x 2.5
Test voltage, rms Power conductors	4000 V
Rated voltage U0/U in accordance with EN 50395 Power conductors	600 V/1000 V

Mechanical data	
Smallest bending radius (fixed installation)	6 x diameter
Smallest bending radius (flexible installation)	155mm
Number of bends, max.	1,000,000
Tensile stress, max. Fixed installation	50 N/mm²
Tensile stress, max. Flexible installation	20 N/mm²
Torsional stress	Absolute 30°/m
Connection type	Straight connector (fixed cable outlet direction)

Length

5.0 m



Figure similar

MLFB-Ordering data

6FX3002-5CL12-1AF0

Technical data

Ambient temperature

Operation with permanently installed cable	-25 ... 80 °C
Kind of connection cable	Power cable
Material of the cable sheath	PVC
Type of insulation	PVC
Degree of protection	IP65
Standard for behavior in fire: flame resistance	EN 60332-1-1 to 1-3
Oil resistance	EN 60811-2-1 (mineral oil only)
Verification of suitability, CE marking	Yes
Verification of suitability, UL approval	Yes
Verification of suitability, RoHS conformity	Yes