

FEATURES

- Plan Shank
- Various lengths
- HSS for performance and safety
- Perfect for general workshop and maintenance use

RS PRO HSS Twist Drill Bit, 16mm x 156mm

RS Stock No.: 784-4826



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

Brought to you by RS PRO, a range of jobber drill bits suitable for high-speed metal, wood and plastic drilling. Designed as a twisted drill bit, these attachments guarantee excellent performance and will be an asset to your application. All models are highly reliable and excellent quality.

General Specifications

Drill Bit Type	Twist Drill Bit	
Туре	Twist	
Material	70% flute length is made of HSS	
Surface	Black Finish	
Shank Type	Reduced	
Drilling Application	Construction, electrical or masonry applications	

Mechanical Specifications

Overall Length	156mm
Point Angle	118°
Diameter	16mm
Flute Length	83mm

Drill Bits



RS Art.No.	Dia.(mm)	Overall Length(mm)	Flute Length(mm)
7844816	14.00	156	83
7844810	14.50	156	83
7844829	15.00	156	83
7844822	15.50	156	83
7844826	16.00	156	83
7844835	16.50	156	83
7844838	17.00	156	83
7844832	17.50	156	83
7844841	18.00	156	83
7844844	18.50	156	83
7844848	19.00	156	83
7844857	20.00	156	83

