




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.



LOC	DIST	REVISIONS			
		P	LTR	DESCRIPTION	DATE
J	—		D	REVISED	26AUG10




断面 B-B
SECT.



断面 C-C
SECT.



0.5+タブにかん合
MATE WITH 0.5+ TAB



断面 A-A
SECT.

AWG#30~#28 0.05~0.09mm ²	φ0.6~φ1.2	COPPER ALLOY,FINISH:CONTACT AREA Au 0.38μ m MIN,OVER Ni 1.27μ m MIN 材料：銅合金,下地：Niめっき1.27μ m以上,接点部：金めっき0.38μ m以上	1827569-2
WIRE RANGE 導体断面積	INSULATION DIA 被覆外径	MATERIAL 材料	PART No. 型番
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.KUDO 04MAR2005 CHK D.MITSUGI 04MAR2005 APVD D.MITSUGI 04MAR2005	Tyco Electronics Corporation Kawasaki, Japan
DIMENSIONS: 単位： 耗 mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差	PRODUCT SPEC 製品規格 108-78268	DYNMIC D1000 SERIES REC CONTACT S TYPE REEL
0 PLC ± 0.3 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± 3deg	FINISH 仕上	APPLICATION SPEC 取付適用規格 114-5377	
MATERIAL 材料		WEIGHT —	SIZE A3
CUSTOMER DRAWING		CAGE CODE 00779	DRAWING NO 番号 C-1827569
		SCALE 尺度 10:1	SHEET 1 OF 1
		REV D	