

FEATURES

- Designed using strong polyethylene (PE)
- Easy to assemble – no tools are required
- Moisture resistant and impact proof - will not rust
- Four non-marking wheels
- Integrated handle on the top shelf

RS PRO 3 Shelf PE Trolley, 610 x 460mm, 150kg Load

RS Stock No.: 444-2391



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These RS Pro Plastic shelf trolleys (or carts) are great for transporting goods and create greater mobility throughout the workplace. The trolley is easy to move around with the four swivel castor wheels of which two have brakes, to ensure you can lock it securely in place. The top shelf of the trolley is fitted with two hand grips. This trolley is made up of three anti-slip shelves with lipped edges in Polypropylene making it suitable for harsh environments.

General Specifications

Type	Shelf
Number of Levels	3
Wheel Type	Castor
Wheel Features	Braked, Swivel
Frame Material	PE
Applications	Canteens, Offices, Workshops, Warehouses, Garages

Mechanical Specifications

Lipped Edge Height on Shelf	6
Load Capacity	150kg
Wheel Diameter	100mm
Shelf Clearance Between Each Shelf	315mm

Trolley Size	
Dimension	860mm x 670mm x 460mm
Depth	460mm
Width	670mm
Height	860mm

External Shelf Size	
Platform Dimension	610mm x 460mm
Platform Length	610mm
Platform Width	460mm

Internal Shelf Size	
Dimension	595mm x 444mm
Length	595mm
Width	444mm



UTILITY TRAY TROLLEY RANGE								
Trolley Size HxWxD (mm)	No. of Shelves	External Shelf Size LxW (mm)	Internal Shelf Size LxW (mm)	Lipped Edge Height on Shelf (mm)	Shelf Clearance Between Each Shelf (mm)	Wheel Dia (mm)	Capacity (Kgs)	RS Stock No.
860 x 670 x 460	3	610 x 460	595 x 444	6	315	100	150	2255971
860 x 670 x 460	3	610 x 460	595 x 444	6	315	100	150	4442391
860 x 885 x 610	2	810 x 610	812 x 595	12	630	100	180	2256003
835 x 885 x 610	3	810 x 610	812 x 595	12	275	100	180	2256019
975 x 885 x 610	3	810 x 610	812 x 595	12	275	200	350	7898548