

ALPHA

8377U00100P62

EAN 4031582491104

Swivel castor with total lock, tail end of castor, plate fitting. stainless housing Wheel centre made of Polyamide, plain bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	100 mm
Wheel width	36 mm
Size of Plate	105 x 85 mm
Plate hole centres	80/77 x 60 mm
Plate hole	9 mm
Offset	39 mm
Swivel Interference	224 mm
Overall height	128 mm
Temperature	- 25 / + 80 °C
Standard	EN_12532
Swivel Radius	112 mm
Hardness of tread	Shore D 75
Load capacity	150 kg
Load capacity (static)	300 kg

Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●