Simply Silent[™] Contour C6 6"/150mm axial extract fan range


Bune

The Simply Silent[™] Contour C6 intermittent extract fan range has been designed to blend seamlessly with the surrounding décor. These fans control humidity, odours and mould growth effectively in kitchens, utility rooms, larger bathrooms and individual offices. The Contour 6 range has two speeds, selectable at install. Long-life ball-bearing motors suppress motor noise.

Flow straighteners guide air through the duct, reducing turbulence. Optimised impeller blade design maximises performance, while minimising noise.

/ A cone behind the front baffle directs air straight onto the impeller for optimal airflow efficiency.






Product Features	C6S	C6TS	C6PS	С6НТЅ	C6R	C6TR	C6PR	C6HTR
Reference Number	93170AW	93172AW	93174AW	93176AW	93171AW	93173AW	93175AW	93177AW
Trade Price	£66.66	£74.99	£74.99	£99.99	£66.66	£74.99	£74.99	£99.99
Design					•	•	•	•
Standard	1				1			
Timer		1		1		1		1
Pullcord			1				1	
Humidistat				1				1
Backdraught Shutter	1	1	1	1	1	1	1	1

Product Selector	C6	
Speeds	2	
Extract Performance (I/s)	54/61	
Extract Performance (m ³ /h)	194/217	
Electrical Power Rating (W)	15/22	
Specific Fan Power (W/I/s)	0.28/0.36	
Sound Pressure Level (dBA@3m)	41/44	
IP Rating	IPX4	

Low Speed			High Speed		
Static Pressure (Pa)	Flow rate in m ³ /h		Static Pressure (Pa)	Flow rate in m ³	
0	193.46		0	218.32	
3.2	182.99		4.2	208.20	
5.8	172.59		9.2	196.35	
9.2	161.51		13	183.73	
12.2	149.60		16.3	170.17	
14.2	136.66		19.8	155.44	
16.3	122.34		23.9	139.14	
17.8	106.08		29.5	120.64	
19.4	86.79		35.8	98.68	
21.6	61.62		42.2	70.05	
23.5	0.00		48.6	0.00	



Øxpelair

ANCILLARIES We recommend the Simply Silent 150mm Easy Fit Wall Kit to allow fuss-free fitting from the inside. See page 118 for further information.