




Switches > Toggle Switches



Contact Current Rating: **.4 A**
Configuration (Pole-Throw): **Double Pole - Double Throw**
Operating Function: **On On On**
Number of Positions: **3**
Operating Voltage: **20 VDC**

Features

Product Type Features

Sealed Device	Yes
Switch Connection Type	Wire Lugs
Toggle Style	Baton Long
Switch Type	Toggle Switch

Configuration Features

Configuration (Pole-Throw)	Double Pole - Double Throw
Operating Function	On On On
Number of Positions	3

Electrical Characteristics

Contact Resistance	10 mΩ
Insulation Resistance	1000 MΩ
Dielectric Withstanding Voltage (Max)	1000 VAC
Contact Current Rating	.4 A
Operating Voltage	20 VAC



Body Features

Actuator Finish	Nickel
Product Orientation	Horizontal
Bushing Style	Threaded
Bushing Thread Size	1/4-40

Contact Features

Contact Base Material	Copper
Switch Contact Plating Material	Gold

Mechanical Attachment

Product Mount Type	Panel Mount
--------------------	-------------

Housing Features

Process Sealed	No
----------------	----

Dimensions

Toggle Length	10.4 mm[.41 in]
	.35 in

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (3.7% in 4936246) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent



chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1825136-7
[A101KZQ04](#)

TE Part # 4-1825136-5
[A101SYCQ04](#)

TE Part # 4-1825136-9
[A101SYZQ04](#)

TE Part # 5-1825136-9
[A108P3ZQ04](#)

TE Part # 4-1825136-3
[A101SYAQ04](#)

Also in the Series | [Alcoswitch Gemini A Series](#)

[Rocker Switches\(6\)](#)

[Toggle Switches\(34\)](#)

Customers Also Bought



TE Part #1625862-4
RH73 2A 50G 30% 1000PPM 1K RL

TE Part #9-1614889-6
CPF 0805 4R99 0.1% 25PPM 1K RL

TE Part #5053162047
RNF-100-3/8-4-STK

TE Part #390112-1
SKT,SODIMM,144P,SDRAM3.3V,HIGH

TE Part #1622437-1
LR1 1% 330K

TE Part #2118716-2
STD SHIELD FRAME, CRS-16.50X16.50X3.60MM

TE Part #374472-E
STVTE 160 MI ABCDE VVVV 4-00 GA06 4,0 *

TE Part #2118715-2
STD SHIELD COVER, CRS-16.90X16.90X2.00MM

TE Part #6221-BCE-T-025-001
2.5 kPa Gauge Sensor

TE Part #6221-BCE-T-005-001
5KPA GAUGE SENSOR

Documents

Product Drawings
A211SYZB04

English

CAD Files

Customer View Model
ENG_CVM_CVM_3-1825139-8_A.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_3-1825139-8_A.3d_stp.zip

English

Customer View Model
ENG_CVM_CVM_3-1825139-8_A.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



[SWITCHES_CORE_PROGRAM_CATALOG](#)

English

[GEMINI_SERIES_SWITCHES_QUICK_REF_GUIDE_2-1773458-5](#)

English