

FEATURES

- **LED Bulb Type:** Offers energy efficiency and long service life
- **Flashing Light Effect:** Provides clear visual alerts to enhance safety
- **Sound Level up to 92 dB:** Ensures audible alerts in noisy environments
- **IP43 Rating:** Suitable for indoor use, protecting against solid objects over 1mm
- **ABS Housing Material:** Durable and resistant to impact, ensuring longevity
- **Wide Operating Temperature Range:** Functions effectively from -20 °C to 50 °C
- **Screw Mount Type:** Easy and secure installation

RS PRO LED Horn-Beacon Combination, IP43
Grey Housing

RS Stock No: 658-302



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO Horn-Beacon Combination is designed to provide both audible and visual alerts in industrial environments. Ideal for safety and warning applications, it combines a flashing LED light with a powerful sounder, ensuring clear communication of alerts in noisy settings.

General Specifications

Bulb Type	LED
Housing Colour	Grey
Lens Colour	Orange
Light Effect	Flashing
Mount Type	Screw
Number of Tones	1
Product Type	Horn-Beacon Combination
Sounder Type	Sounder Beacon

Electrical Specifications

Current Consumption	0.04 A
Current Type	AC
Maximum Supply Voltage	240 V ac

Mechanical Specifications

Housing Material	ABS
------------------	-----

Protection Category

IP Rating	IP43
-----------	------

Operation Environment Specifications

Maximum Operating Temperature	50 °C
Minimum Operating Temperature	-20 °C

Measurement Specifications

Maximum Sound Level	92 dB
Minimum Sound Level	88 dB

Approvals

Standards/Approvals	CE, EAC
---------------------	---------