

PSM02 0.2 ... 2 bar G 1/4 B acc. to ISO228-1

pressure switch mechanical model PSM02

Item number: 14087348

Quantity: 1 pcs.

Order code: PSM02-11-30B 20-P131Z-Z-3ZZ-ZZZZZZZZ2 1 AZZZ

Overview: PSM02 0.2 ... 2 bar G 1/4 B acc. to ISO228-1
Maximum system pressure: 60 bar
Material process connection: steel galvanised
measuring principle: Membrane
Diaphragm material: NBR -20 ...80 °C
Case material: steel galvanised
Switching function: SPDT
Adjustable
switching capacity: acc. to Datasheet
Electrical connector: DIN EN 175301-803 with cable box
Restrictor: without
Certificates: without
Type of packaging: single/multiple packaging (from 10 piece) acc. to order quantity
Packaging instruction see: 14378446
Specifications according to data sheet: PV 34.82

Details: pressure switch mechanical model PSM02
Specifications according to data sheet: PV 34.82
Packaging instruction see: 14378446
measuring principle: Membrane
Material process connection: steel galvanised
Case material: steel galvanised
Switching function: SPDT
Process connection WN02.062: G 1/4 B acc. to ISO228-1
Diaphragm/sealing material: NBR
Electrical connector: DIN EN 175301-803 with cable box
Certificates: without
Setting of switching point: Adjustable
switching capacity: acc. to Datasheet
Restrictor: without
Type of packaging: single/multiple packaging (from 10 piece) acc. to order quantity
Unit: bar
Maximum system pressure: 60 bar
Setting range: 0.2 ... 2 bar