

EPIC ULTRA



Epic Ultra H-B 6

70250202 - ULTRA H-B 6 TG LB 9-17 BRUSH

70250205 - ULTRA H-B 6 TS LB 9-17 BRUSH



- Optimal, low-resistance 360° screening
- Space saving due to compact dimensions

70250206 - ULTRA H-B 6 AG LB

70250209 - ULTRA H-B 6 SGR LB 9-17 BRUSH



- All-purpose due to high corrosion resistance and a high environmental protection
- Housings with addition BRUSH come with BRUSH cable screen contacting

Epic Ultra H-B 10

70250212 - Ultra H-B 10 TS QB 11-21 BRUSH

70250213 - Ultra H-B 10 AG QB



- Faster than any other comparable system
- Mateable with standard housings

Epic Ultra H-B 16

70250216 - Ultra H-B 16 TS QB 11-21

70250217 - Ultra H-B 16 AG QB



- Corrosion resistant according to DIN EN 6988
- For higher mechanical stress

Epic Ultra H-B 24

70250221 - Ultra H-B 24 TS QB 11-21

70250222 - Ultra H-B 24 AG QB



- Lever and bolts: stainless steel
- Housing: Zinc die cast nickel plated

Epic Ultra H-B kits

70250202 + 10190000 - Ultra H-B 6 TG LB 9-17 Brush Male
70250202 + 10191000 - Ultra H-B 6 TG LB 9-17 Brush Female
70250205 + 10190000 - Ultra H-B 6 TS LB 9-17 Brush Male
70250205 + 10191000 - Ultra H-B 6 TS LB 9-17 Brush Female
70250206 + 10190000 - Ultra H-B 6 AG LB Male
70250206 + 10191000 - Ultra H-B 6 AG LB Female
70250209 + 10190000 - Ultra H-B 6 SGR LB 9-17 Brush Male
70250209 + 10191000 - Ultra H-B 6 SGR LB 9-17 Brush Female
70250212 + 10192000 - Ultra H-B 10 TSQB 11-21 Brush Male
70250212 + 10193000 - Ultra H-B 10 TSQB 11-21 Brush Female

70250213 + 10192000 - Ultra H-B 10 AG QB Male
70250213 + 10193000 - Ultra H-B 10 AG QB Female
70250216 + 10194000 - Ultra H-B 16 TSQB 11-21 Brush Male
70250216 + 10195000 - Ultra H-B 16 TSQB 11-21 Brush Female
70250217 + 10194000 - Ultra H-B 16 AG QB Male
70250217 + 10195000 - Ultra H-B 16 AG QB Female
70250221 + 10196000 - Ultra H-B 24 TSQB 11-21 Brush Male
70250221 + 10197000 - Ultra H-B 24 TSQB 11-21 Brush Female
70250222 + 10196000 - Ultra H-B 24 AG QB Male
70250222 + 10197000 - Ultra H-B 24 AG QB Female

