



Datasheet

RS PRO SPIRALFLEX NYLON - SWN Series

Stock number: See Table



1. Polyamide 12 (PA12)



Applications:

- Automotive
- Trailer manufacture

Designed to protect all types of hydraulic and pneumatic hoses and cables. This cost-effective cover protects against shocks, abrasion and deterioration, helping reduce your equipment downtime and keeping maintenance costs to a minimum.

SpiralFlex spiral wrapping is made from the highest quality PA12 (Nylon) can easily be added to existing or new hydraulic or pneumatic assemblies without the use of any tools. Comes in handy recyclable dispensing cartons for ease of use.

Key Features:

- Easy to use with singular hose, bundle of hoses, cables and multi-lines.
- Manufactured with smooth round edges and surfaces in order to prevent damage to hose assemblies or equipment during use and mounting.
- Suitable for a wide temperature range -40°C to +138°C and for use with all hydraulic fluids including glycol and phosphate based products.

Sizes:


Available in 20m and 50m coils

Colours:

Black

Packaging:

Supplied boxed for ease of handling.



| Product Ref | Size Range | External Diameter | Internal Diameter | Wall Thickness | Weight per coil | Coil Length |
|-------------|------------|-------------------|-------------------|----------------|-----------------|-------------|
| 1860583 | 4-8mm | 8mm | 6mm | 1mm | 2.3 Kg | 100m |
| 1860584 | 8-12mm | 12mm | 10mm | 1mm | 2.1 Kg | 50m |
| 1860585 | 12-19mm | 19mm | 16mm | 1.5mm | 4.2 Kg | 50m |
| 1860586 | 19-23mm | 23mm | 20mm | 1.5mm | 5.2 Kg | 50m |
| 1860587 | 23-25mm | 25mm | 22mm | 1.5mm | 2.8 Kg | 25m |
| 1860589 | 25-29mm | 29mm | 26mm | 1.5mm | 3.3 Kg | 25m |
| 1860590 | 29-34mm | 34mm | 30mm | 2mm | 5.2 Kg | 25m |