

Literature holder FLEXIPLUS 2 A4 landscape magnetic

Article number	1709022060	Sales unit quantity	1 Set
Colour	Black	Sales unit EAN	4005546742632
Packaging unit	1 set	Packing weight (gross)	606.2 G
Base EAN	4005546742632	Country of origin	DE



Product description

- Literature holder with 2 compartments with magnetic fixing for information materials in A4 landscape format
- Ideal for information materials on metallic walls in showrooms, in waiting areas and at trade fairs and in production areas.
- Load capacity of approx. 3 kg
- Inner dimension compartment: 340 x 250 x 23 mm [W x H x D]

Product features

Outer width (mm)	340
Outer height (mm)	270
Outer depth / length	105 mm
Format / Format for	A4+
Orientation Format	Landscape
Brand	DURABLE
Exeternal wall mounting width (mm)	105

Literature holder FLEXIPLUS 2 A4 landscape magnetic

Exeternal wall mounting height (mm)	270
Exeternal wall mounting depth (mm)	340
Inner width (mm)	320
Inner height (mm)	250
Inner depth (mm)	23
Number of Sections	2
Opening for documents	Top
Extendable	No
Recessed slot for easy access	No
Max. load capacity	Up to approx. 3 kg
Country of Origin	Germany
Base / mount type	Magnetic wall mount