

Eaton 105215

Catalog Number: 105215

Eaton Moeller series xPole - Busbar. EV busbars 4Ph., 16HP, 63A for PLS. CLS. PKN., PFIM, PFHM, PFNM

General specifications



Product Name
Eaton Moeller series busbar

Catalog Number
105215

EAN
4015081050123

Product Length/Depth
28 mm

Product Height
12 mm

Product Width
285 mm

Product Weight
0.13 kg

Compliances
RoHS conform

Product specifications

Used with

EVG

Busbar

Type

Busbar

EVG

Features

Insulated

Accessory/spare part type

Busbar for residual current circuit breakers

Busbar for miniature circuit breaker

Busbar for combined residual current/power circuit breaker

Electric connection type

Fork

Rated surge voltage

4 kV

Rated uninterrupted current (Iu)

63 A

Suitable for number of devices

8

Number of poles

Four-pole

Color

Other

Rated short-time withstand current (Icw)

0 kA

Cross section

10 mm²

Number of modular spacings

16

Number of phases

4

Pitch dimensions

0 mm

Rated operational voltage (Ue) - max

415 V

Resources

Declarations of conformity

[DA-DC-03_EVG](#)

Drawings

[eaton-busbar-3d-drawing.jpg](#)

[eaton-mcb-busbar-3d-drawing-006.eps](#)

Rated conditional short-circuit current (Iq)

25 kA

Functions

Busbar

Suitable for

8 devices

Devices with N-busbar



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia