

General Information

Extended Product Type:	4125MVS6WH
Product ID:	2CMA162792R1000
EAN:	7392696627924
Catalog Description:	Switched interlocked socket-outlet, vertical, Heavy Duty, 6h, 125A, IP67, 3P+N+E
Long Description:	Switched Interlocked Socket Outlet, vertical, Heavy Duty, earthing sleeve position 6h, rated current 125A, IP67 watertight, 3-poles+neutral+earth

Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Switched Interlocked Socket Outlets, Vertical

Ordering

EAN:	7392696627924
Minimum Order Quantity:	1 piece
Country of Origin:	Czech Republic (CZ)

Dimensions

Product Net Width:	180 mm
Product Net Height:	260 mm
Product Net Length:	460 mm
Product Net Depth:	260 mm
Product Net Weight:	4.3 kg

Container Information

Package Level 1 Width:	260 mm
Package Level 1 Length:	180 mm
Package Level 1 Height:	490 mm
Package Level 1 Gross Weight:	4.3 kg
Package Level 1 EAN:	7392696627924
Package Level 1 Units:	1 piece

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2007 Q1
--------------	---

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	2CMC700005D0001
Environmental Information:	2CMC700001D0002
RoHS Information:	2CMC700057D0001

Additional Information

Additional Information:	Cable entry, knock-outs Ø40+50mm on top and drill marks on bottom
Cable Cross-Section:	16 ... 70 mm ²
Cable Entry Position:	Top
Cable Outlets Per Side:	1xØ40+1xØ50 mm on top and drill marks on bottom
Color:	Red
Degree of Protection:	acc. to IEC 60529 IP67
Enclosure Material:	Thermoplastic polyester (PBT)
Frequency (f):	50 Hz 60 Hz
Function:	Switched Interlocked Socket outlet, vertical, Heavy Duty
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#4125MVS6WH
Mounting Type:	vertical
Number of Auxiliary Contacts NO:	1
Number of Poles:	5
Object Classification Code:	2CMT005069
Product Main Type:	MVS
Product Name:	Industrial Switched Interlocked Socket Outlet
Protection Type:	Watertight heavy duty
Rated Current (I _n):	125 A

Rated Voltage (U_r):	346 ... 415 V
RoHS Date:	L23
Standards:	IEC 60 309-1, -2, -4
Suitable For:	Switched Interlocked Socket Outlets, Vertical
Suitable for Product Class:	Industrial Plugs and Sockets

Classifications

E-nummer:	2416996
UNSPSC:	39120000

