



(2.54 mm) .100"

BBS, BBL, BHS, BBD, BDL SERIES

MACHINED BOARD STACKING STRIPS

Mates with:

SS, SD, HSS, SL, SDL, ESS, ESD

FEATURES

- Low profile design achieves (3.89 mm) .153" board spacings when mated with SL Series.
- Approach the reliability of a permanent connection with the flexibility of a separable connection.

SPECIFICATIONS

For complete specifications see www.samtec.com?BBS, www.samtec.com?BBL, www.samtec.com?BHS, www.samtec.com?BBD or www.samtec.com?BDL

Insulator Material:
 Black Glass Filled Polyester (BBS, BBD, BBL)
 Black High Temp Nylon (BDL)
 Black Liquid Crystal Polymer (BHS)

Temperature Range:
 -55 °C to +125 °C

Terminal Material:
 Phosphor Bronze or Brass

Plating:
 Au or Sn over 50 μ" (1.27 μm) Ni

RoHS Compliant:
 Yes

Lead-Free Solderable:
 Wave only (BBS, BBD, BBL, BDL)
 Wave, or reflow with all Au (BHS)

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



Note: Some lengths, styles and options are non-standard, non-returnable.

