

Features

- ESD Phillips precision screwdriver.
- PH-0 dimensions 3.0x60mm.
- Blade Ø 3.0mm.
- Total length 160mm.
- Rotating cap.
- Ergonomic anti-slip bi-component handle for a safe, light and comfortable grip.
- Chromo-Vanadium-Molybdenum steel blades with black tips having a black oxide treatment.
- ESD safe handle.
- Laser marking.

RS PRO ESD Phillips precision screwdriver PH-0

RS Stock No.: (0429677)



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

- *Phillips precision screwdriver*
- *Dimensions PH-0 3.0x60mm*
- *Blade Ø 3.0 mm*
- *Rotating cap*
- *Chromo-Vanadium-Molybdenum steel blades with black tips having a black oxide treatment.*
- *ESD ergonomic anti-slip bi-component handle for a safe, light and comfortable grip.*
- *This precision screwdriver is ideal for different applications in microelectronics, jewellery making, laboratory, watch making and repairs, DIY.*

General Specifications

Tip	Phillips
Blade	3 mm Ø
Tip length	3 mm
Tip width	PH-0
Length of the blade	60 mm
Total length	164 mm +/-3 mm
Net weight	19.5 g +/-3 g
Dimensions	PH-0 3.0x60mm
Type of material	Chromo-Vanadium-Molybdenum steel blades with black tips having a black oxide treatment
ESD Safe	YES. Standard IEC 61340-5-1
Handle colour	grey/black