


257A | AUTOMATIC CENTRE PUNCH



Description :

- Simply press the end to release spring impact.
- Impact adjustable by turning the knurled head.
- Acceptable load: 11 to 22 kg.
- Presentation: chrome body, greased tip.
- Length: 163 mm, body Ø 16 mm, shank Ø 7 mm.
- Interchangeable tip: 257.07. Spare tip: 257.10A.

Informations :

	257A
L [mm]	163
[g]	135