



Example image

CHARACTERISTICS

- Outside zinc-plated

TECHNICAL DATA

Product material	Non-alloy steel 1.0034 E195 (EN 10305)
Surface roughness	10 µm
Thermal expansion	0.012 mm/(m·K)
Thermal conductivity, pipe	60 W/(m·K)

Specific thermal capacity 500 J/(kg·K)

ACCESSORIES

- Geberit Mapress pipe cutter R
- Geberit Mapress pipe deburrer
- Geberit Mapress insertion distance template with marker pen

Art. no.	DN	d _o mm	d _i mm	s mm	L m
These articles are suitable for the following system: Geberit Mapress Carbon Steel					
29101	10	12	9.6	1.2	6
29102	12	15	12.6	1.2	6
29103	15	18	15.6	1.2	6
29104	20	22	19	1.5	6

Art. no.	DN	d _ø mm	d _i ø mm	s mm	L m
29105	25	28	25	1.5	6
29106	32	35	32	1.5	6
29107	40	42	39	1.5	6
29108	50	54	51	1.5	6
29158	65	66.7	63.7	1.5	6
29159	65	76.1	72.1	2	6
29160	80	88.9	84.9	2	6
29161	100	108	104	2	6

These articles are suitable for the following system: **Geberit Mapress Carbon Steel (FKM blue)**

29101	10	12	9.6	1.2	6
29102	12	15	12.6	1.2	6
29103	15	18	15.6	1.2	6
29104	20	22	19	1.5	6

<i>Art. no.</i>	<i>DN</i>	<i>d_ø</i> <i>mm</i>	<i>d_i ø</i> <i>mm</i>	<i>s</i> <i>mm</i>	<i>L</i> <i>m</i>
29105	25	28	25	1.5	6
29106	32	35	32	1.5	6
29107	40	42	39	1.5	6
29108	50	54	51	1.5	6
29159	65	76.1	72.1	2	6
29160	80	88.9	84.9	2	6
29161	100	108	104	2	6