



Mobile power LED Lamp ML2705 IP 44

27 x 0,5 W Power LEDs for lighting large areas.
Ideal for indoor and outdoor use, IP 44.

- Uses 80 % less energy than conventional lamps.
- Bright light instantly.
- Low heat generation, no danger of injury.
- LEDs have a very long lifespan, are shock-proof and maintenance-free.
- Housing made of aluminium, powder-coated.
- Stable, shock-absorbing steel-tube frame with ergonomic carrying handle.
- Spotlight can be steplessly rotated and locked.
- Cover made of break resistant plastic.
- In colourful display-packaging.
- Luminous flux: ~ 1080 lm
- Energy efficiency class: A



Article No.	EAN-Code	UP	Cable length	Cable	LEDs	Lamp efficacy	Colour temperature	Output	Voltage
1 17332 3	612895	1	2 m	H05RN-F 3G1,0	27	64 lm/W	6400 K	~ 17 W	240 V
1 17332 3 110	614462	1	2 m	H05RN-F 3G1,0	27	64 lm/W	6400 K	~ 17 W	110 V



Mobile Professional LED spotlight Brobusta® ML3001 IP 65

30 x 1 W high-output LEDs with special light scattering for lighting large areas.
Ideal for hobbyists, workshops and construction sites, suitable for indoor and outdoor use, IP 65.

- Uses 80 % less energy than conventional lamps.
- Bright light instantly.
- Low heat generation, no danger of injury.
- LEDs have a very long lifespan, are shock-proof and maintenance-free.
- Sturdy aluminium die-cast case with cooling fins for optimum heat dissipation.
- Stable, shock-absorbing steel-tube frame with ergonomic carrying handle.
- Spotlight can be steplessly rotated and locked.
- With safety glass.
- In colourful display-packaging.
- Energy efficiency class: A



Article No.	EAN-Code	UP	Cable length	Cable	LEDs	Lamp efficacy	Colour temperature	Output	Luminous flux
1 17333 3	612901	1	5 m	H07RN-F 2x1,0	30	63 lm/W	6400 K	~ 31 W	~ 2000 lm