

Previously known as: MICROGARD® 2000 Overshoes - Model 417

Safety overshoes designed with superior breathable microporous laminate technology.

- **Certified protection:** AlphaTec® 2000 STANDARD Overshoes Bound - Model 417 provides a proven protective barrier against low-concentration liquid chemicals and liquid and particulate biological hazards
- **Increased comfort:** To ensure greater comfort and mitigate heat stress, these protective overshoes are made of moisture vapor permeable fabric
- **Advanced ergonomics:** As they are designed with greater wearer comfort and safety in mind, these safety overshoes ensure an optimized fit
- **Reduced contamination risks:** AlphaTec® 2000 STANDARD Overshoes Bound - Model 417 has a low lint composition, which alleviates contamination risks



Industries

- Life Sciences
- Metal fabrication
- Food Processing

Applications

- Clean room cleaning and preparing
- Production line support & maintenance
- Maintenance of plant and machines
- Veterinary Services
- Cleaning of plant and machines
- Body painting including surface inspection

KEY FEATURES & BENEFITS

- **Protective barrier:** Enhanced biological and chemical resistance
- **Moisture vapor permeable fabric:** Breathable personal protection
- **Optimized fit:** Increased comfort and safety levels

Material Diagram



Seam Diagram



Performance Standards



EN ISO 13688:2013

Product Information

Product Information	
Available Sizes	39-42, 42-46, 46-48
Color	White
Country Of Origin	China, Sri Lanka
Packaging Overview	50 pairs every compressed bag
Product Material	Microporous polyethylene Laminate non-woven
Product Reference	2000 Overshoes - Model 417
Standards Overview	CE CATEGORY III (Type PB (6)-B, EN 14126)
Seam Type	Bound
Shelf Life	5 years
Style Number	W20B417

Suit components & accessories

Suit Components and Accessories	
Design Features	Elasticated opening, bound seams and ESD PVC sole.

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region
Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00

North America Region
Ansell Healthcare Products LLC
T: +1 800 800 0444

Australia
Ansell Limited
T: +61 1800 337 041

Asia Pacific Region
Ansell Global Trading Center
T: +603 8310 6688

Latin America & Caribbean Region
Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

