



19-12-H

Flex Head Ratcheting Combination Wrench Set, Holder 12 Pcs

PRODUCT DETAILS

- 12 piece set in plastic holder
- Components: 12 Flex Head Ratcheting Combination Wrenches 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18 and 19 mm
- Finish: Chrome-plated matt finish
- Material: High performance alloy steel
- Hardness: 40-50 HRC
- Standards: ISO 3318 and DIN 3113

PRODUCT ATTRIBUTES

Product			
19-12-H	12	35 x 180 x 250 mm	1724 g

SET CONTENT



Flex Head Ratcheting Combination
Wrench 8 mm, Clip
19-08-1



Flex Head Ratcheting Combination
Wrench 10 mm, Clip
19-10-1



Flex Head Ratcheting Combination
Wrench 11 mm, Clip
19-11-1



Flex Head Ratcheting Combination
Wrench 12 mm, Clip
19-12-1



Flex Head Ratcheting Combination
Wrench 13 mm, Clip
19-13-1



Flex Head Ratcheting Combination
Wrench 14 mm, Clip
19-14-1



Flex Head Ratcheting Combination
Wrench 17 mm, Clip
19-17-1



Flex Head Ratcheting Combination
Wrench 19 mm, Clip
19-19-1