



ENGLISH

Datasheet

# RS Pro HSS Deburring Reamer Tool

RS Stock No: 456-917



RS Pro hand-operated, tapered reamer with straight flutes. Designed for deburring, repairing and finishing of panel holes.

## Features and Benefits

- 1 pc - 3 mm ~ 12 mm high speed steel
- Red-Black double injection grip
- 6 step flutes
- Overall length: 175 mm

## Finish

Chemical black finish with machinery / grounding flute of deburring reamer head and P.P/TPR double injection grip

## Hardness

Heat treated to HRC: 60~66 for HSS reamer head