1362 - 1364 : Threading Set 3/8" - 2" And 1.1/2" - 2" - Metal Case











The + product :

Reversible ratchet for increased manœuvrability.
Ergonomic grip.
Easy head installation and removal.

Description

Capacity:
Steel
Right BSPT: Ø 1/4" to 2"
Left BSPT: Ø 1/4" to 2"
NPT : Ø 1/4" to 2"

Tubular steel handles.
Heads can also be used on Mini Phenix / Phenix III / Phenix IV portable electric threading machine.

For tubes complying with the EN 10255 S and EN 10255 W standards (former NFA 49115 and NFA 49145 standard medium and heavy duty series); only light series tubes are not recommended.

References

Sku	Description	Case	kg
136280	2 single ratchet housings + handle BSPT right : 1/2 - 3/4 - 1 - 1.1/4 - 1.1/2 - 2	670 x 230 x 150 mm	20,000
136281	Single ratchet housing with 2 part handle Single ratchet housing with 3 part handle - BSPT Right 1/2 - 3/4 - 1 - 1.1/4 - 1.1/2 - 2	450 x 345 x 100 mm	17,000
136282	2 single ratchet housings + handle BSPT right : 3/8 -1/2 - 3/4 - 1 - 1.1/4 - 1.1/2 - 2	670 x 230 x 150 mm	20,700
136263	2 single ratchet housings + handle NPT : 1/2 - 3/4 - 1 - 1.1/4 - 1.1/2 - 2	670 x 230 x 150 mm	20,000

Sku	Description	Case	kg
136460	Single ratchet housing + Handle Right BSPT: 1.1/2 - 2	660 x 200 x 110 mm	12,800

