

HIGH FLEXIBILITY HYBRID POLYMER HOSE EXTENSION

FLEXAIR high flexibility hybrid polymer hose extension with
PREVOS1 safety quick couplers



Part number	Length (m)	Temperature min/max (°C)	Max. operating pressure (bar)	Net weight (Kg)	Profile
RAL RISB1010	10.00	-15.00 / 60.00	12.00	1,73	ISO 6150B
RAL RESB1010	10.00	-15.00 / 60.00	12.00	1,638	EUROPEAN
RAL RBSB1010	10.00	-15.00 / 60.00	12.00	1,7	BRITISH

Part number	Ø int/ext (mm)
RAL RISB1010	10.00 / 15.50
RAL RESB1010	10.00 / 15.50
RAL RBSB1010	10.00 / 15.50