



### Main

Range of product	Odace
Product or component type	LED
Product specific application	Replacement lamp
Type of packing	Paint cover

### Complementary

Light source colour	Blue
Product destination	Fixing frame
Fixing mode	Clip-in
Colour tint	Grey (RAL 7030)
Temperature rise	25 °C
Current consumption	0.15 mA
Number of cables	2
Material	PC (polycarbonate) GF10 FR: casing
Embedding depth	12.5 mm
Net weight	0.001 kg

### Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...45 °C
Standards	EN 60669-1 2006/95/EEC
Product certifications	LCIE: NF 619318A N NF
Environmental characteristic	Petrol Oil Window-cleaning fluid UV resistant Bleach Alcohol Liquid soap Acetone

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations