


Technical sheet

BAR2020GR

Polypropylene safety barrier 2 m – with feet - grey


Polypropylene barrier designed to secure work areas. Available in grey RAL 7035 and orange RAL 2000. Dimensions: 2000 x 1000 mm (usable) and 2080 x 1015 mm (overall). Easy assembly with a two-point connection system. Fitted with Class 1 reflective strips (25 cm + 10 cm) for high visibility, with Class 2 available as an option. Rotating and movable feet allow flat storage for space saving. Rust-proof. Stability can be increased with a 25 kg base (BASE2500) or by ballasting with up to 20 liters of water (up to the connection level). Compatible with solar accessories (lamp or flash) to enhance visibility.











Customs code	3926909090
EAN	3321360034496

Color : Grey

Material : Polypropylene

Specifications :

- Polypropylene safety barrier.
- Easy assembly thanks to its two-point connection system.
- Class 1 reflective adhesive.
- Can be weighted with water if necessary.
- Rust-resistant.
- Movable/rotating feet allow for flat storage to save space.
- Weighted bases available as an option.

Width (mm)	Height (mm)	Number of barriers	Type of fixing	Net weight (kg)
2000	1000	1	without base	19,00

VISO
www.viso-cpn.com

VISO - 7 avenue Arago - ZI de la Vigne aux Loups - 91380 CHILLY-MAZARIN - France
Tél. + 33 (0)1 69 53 46 70 - Fax + 33 (0)1 69 53 46 80 - contact@viso-cpn.com / commande@viso-cpn.com