



R-297

Heavy-duty impact protection gloves, ensuring hand safety with added cut resistance



Impact Liquid Spray and Splash



Heavy Duty

Heavy-duty impact protection gloves, ensuring hand safety with added cut resistance

- **Specialized protection:** RINGERS® R297 heavy-duty impact gloves are developed with innovative RINGERS® F3 Technology™ and a patented TPR (thermoplastic rubber) design, delivering superior impact protection for the knuckles, thumb and full length of the fingers
- **Added defenses:** With a padded palm and a Kevlar®-stitched liner, these safety gloves provide abrasion and cut resistance, granting users dependable hand protection for heavy-duty applications
- **Strengthened grip:** Thanks to a durable grip system on the palm and fingers, they also deliver excellent grip
- **Enhanced features:** These RINGERS® gloves feature an extended airprene wrist closure with a practical TPR pull tab, as well as an increased visibility external surface, which helps improve workplace safety



Industries

- Manufacturing
- Oil and gas
- Construction
- Emergency Medical Services
- Utilities

Applications

- Engagement and release of drill string slips
- Chaining up pipes
- Installation and dismantling of rigs
- Preparation of site - unloading of lines and valves
- Handling iron
- Handling of tools
- Seizing structural and body parts
- Unloading worked parts



R-297

Heavy-duty impact protection gloves,
ensuring hand safety with added cut
resistance

Key Features

- **Patented TPR design:** Knuckles, thumb and finger-length impact protection
- **Padded palm with Kevlar® liner:** For durable, cut-resistant gloves
- **Durable grip system on palm and fingers:** Enhanced grip performance

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



ANSI/ISEA 138-2019



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	PACKAGE
RINGERS® R297	Liner Material: Kevlar® Cuff Style: Extended airprene wrist closure		7, 8, 9, 10, 11, 12, 13	5 pairs/bag, 10 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306.
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

