

## FEATURES

- **UV Resistant:** Suitable for outdoor use, resisting degradation from sunlight.
- **High Tensile Strength:** Withstands up to 22 kg, ensuring robust cable bundling.
- **Wide Temperature Range:** Operates between -40 °C and 85 °C, suitable for diverse environments.
- **Non-Releasable Design:** Provides a secure and permanent fastening solution.
- **Complies with RoHS and UL 94HB Standards:** Ensures safety and reliability in various applications.

## RS PRO 250mm Nylon Cable Tie, Non-Releasable

RS Stock No: 656-095



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

These RS PRO cable ties are designed for securing and organising cables efficiently. Made from durable nylon, they are ideal for use in various environments where cable management is essential. The non-releasable design ensures a secure hold, making them suitable for permanent installations.

### General Specifications

Colour	Black
Product Type	Cable Tie
Sub Type	Non-Releasable
Tensile Strength	22 kg

### Protection Category

Fire Behaviour	UL 94HB
UV Resistant	Yes

### Mechanical Specifications

Length	250 mm
Material	Nylon
Maximum Bundle Diameter	68 mm
Width	4.8 mm

### Operation Environment Specifications

Maximum Operating Temperature	85 °C
Minimum Operating Temperature	-40 °C

### Approvals

Standards/Approvals	RoHS, UL94HB
---------------------	--------------