

# Product data sheet

Specifications



2 side panels for plinth.  
400x200mm. Folded sheet steel.  
RAL 7022. IP 30. IK 10.

NSYSPS4200SD

## Main

|                                    |   |
|------------------------------------|---|
| Range                              | Spacial   |
| Accessory / separate part category | Enclosure accessory                               |
| Product or component type          | Plinth side panel                                 |
| Anwendung                          | Multi-purpose                                     |
| Nennmaße des Gehäuses              | -   |
| Device composition                 | fixing elements<br>4 corner cover<br>4 side panel |
| Range compatibility                | Spacial SD<br>Spacial S3D<br>Spacial CRN          |
| Mounting support                   | Front plinth                                      |

## Complementary

|                |                        |
|----------------|------------------------|
| Fixing mode    | By screws              |
| Colour         | Grey (RAL 7022)        |
| Surface finish | Epoxy-polyester powder |
| Height         | 200 mm                 |
| Width          | 400 mm nominal:        |
| Depth          | 400 mm                 |

## Environment

|                         |  |
|-------------------------|--|
| IP degree of protection | IP30 (complete plinth)                           |
| IK degree of protection | IK10 (resistance to external mechanical impacts) |

## Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Weight             | 1.832 kg |
| Package 1 Height             | 6 cm     |
| Package 1 width              | 21 cm    |

---

|                  |         |
|------------------|---------|
| Package 1 Length | 21.5 cm |
|------------------|---------|

---

## Offer Sustainability

---

|                          |                       |
|--------------------------|-----------------------|
| Sustainable offer status | Green Premium product |
|--------------------------|-----------------------|

---

|                  |                                   |
|------------------|-----------------------------------|
| REACH Regulation | <a href="#">REACH Declaration</a> |
|------------------|-----------------------------------|

---

|                    |     |
|--------------------|-----|
| REACH free of SVHC | Yes |
|--------------------|-----|

---

|                   |   |
|-------------------|---|
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a> |
|-------------------|---|

---

|              |     |
|--------------|-----|
| Mercury free | Yes |
|--------------|-----|

---

|                            |                     |
|----------------------------|---------------------|
| RoHS exemption information | <a href="#">Yes</a> |
|----------------------------|---------------------|

---

|                       |   |
|-----------------------|---|
| China RoHS Regulation | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information |
|-----------------------|---|

---

|                          |   |
|--------------------------|---|
| Environmental Disclosure | <a href="#">Product Environmental Profile</a> |
|--------------------------|---|

---

## Contractual warranty

---

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

---